



Model	A	B	C	D	E
HSR048A1-N*	480	205	164.4	287°	406.53
HSR055A1-N*	550	275	142.4	300°	364.32
HSR065A1-N*	650	375	194.0	300°	287.62

Type	ST(mm)	L1	L2	L3
Standard	*=10: 100	555.2	120	220
Standard	*=20: 200	655.2	20	220
Standard	*=32: 320	775.2	-100(*1)	220
Bellows	*=17: 170	662.1	20	190
Bellows	*=29: 290	782.1	-100(*1)	190

Note1) If the length of the Z-axis is 290, 320 mm, the lowest end of the Z-axis motion range reaches the lower position than the robot mount surface. Make sure that the Z-axis does not contact with other objects.

Unit: mm