



Model	A	B	C	D	E
HSSR048A1-N*	480	205	164.4	287°	406.53
HSSR055A1-N*	550	275	142.4	300°	364.32
HSSR065A1-N*	650	375	194.0	300°	287.62

Type	ST(mm)	L1	L2	L3
Standard	*=10:100	587.5	152.3	487.5
Standard	*=20:200	687.5	52.3	487.5
Standard	*=32:320	807.5	-67.7 (*1)	487.5
Bellows	*=17:170	687.5	45.4	517.5
Bellows	*=29:290	807.5	-74.6 (*1)	517.5

Note1) If the length of the Z-axis is 290, 320 mm, the top end of the Z-axis motion range reaches the higher position than the robot mount surface.
Make sure that the Z-axis does not contact with other objects.

Unit : mm